

# Accu-LABS INC.

4831 S. Whipple Avenue  
Chicago IL 60632  
Phone: 773.523.3100 Fax: 773.523.4008  
[www.accu-labs.com](http://www.accu-labs.com)

**A2LA Accredited ISO/IEC 17025:2005 Certificate # 2558.01**

## **953SST STAINLESS STEEL BRIGHT DIP**

Accu-Labs 953SST is a bright dip for 300 series stainless steel, the 304 steel and the 52 alloy. Accu-Labs 953SST leaves the part with a clean bright surface.

**GUIDELINES FOR USE:** Pretreatment: The metal should be completely free of any grease, oil or shop oil. For parts that are severely oxidized or have uneven oxide, it is preferable to descale the parts prior to bright dipping.

- Concentration:** Use concentrated as is
- Time of Immersion:** 3-10 minutes depending on condition of the parts and degree of desired brightness
- Temperature:** 140-170°F **USE IN A WELL VENTILATED AREA!**
- Tank:** Glass lined, Kel F lined, acid proof ceramic or polypropylene
- Heaters:** Pyrex steam coils, Karbate steam coils, tantalum steam coils, quartz sheathed electric heaters
- Rinsing:** Rinse well after bright dipping

**CAUTION:** Use proper personal protective equipment when handling or working with this product. Ventilation is advised; read MSDS prior to use.

**DISCLAIMER:** *The information contained in this bulletin is to the best of our knowledge true and accurate. Because use and conditions are beyond our control, no guarantee is expressed or implied for the above suggestions or recommendations. Accu-Labs, Inc. will not incur any liability in connection with the use of these suggestions or technical data.*